


MRA-4BA Cut Sheet



NITRA pneumatic valve manifold, aluminum, rectangular, 1000 psi maximum operating pressure, (4) stations, (1) 1/8in female NPT inlet(s), (4) #10-32 female threaded outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-4BA>

Technical Specifications

Brand	NITRA
Item	Pneumatic Valve manifold
Material	Aluminum
Shape	Rectangular
Number of Stations	4
Maximum Operating Pressure	1000 psi
Inlet Port	(1) 1/8in female NPT
Outlet Port	(4) #10-32 female threaded
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None