

MRA-4CB-90 Cut Sheet



NITRA pneumatic valve manifold, aluminum, black, rectangular, 1000 psi maximum operating pressure, (4) stations, (2) 1/4in female NPT inlet(s), (8) 1/8in female NPT outlet(s), 90-degree orientation, standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-4CB-90>

Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas
Material	Aluminum
Color	Black
Shape	Rectangular
Number of Stations	4
Maximum Operating Pressure	1000 psi
Inlet Port	(2) 1/4in female NPT
Outlet Port	(8) 1/8in female NPT
Mounting Hole Spacing	Standard
Hole Orientation	90-degree

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MRA-4CB-90.pdf>
See store item page for other formats.