

# MRA-6ED-W Cut Sheet

NITRA pneumatic valve manifold, aluminum, black, rectangular, 1000 psi maximum operating pressure, (6) stations, (2) 1/2in female NPT inlet(s), (6) 3/8in female NPT outlet(s), wide hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-6ED-W>

## Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas
Material	Aluminum
Color	Black
Shape	Rectangular
Number of Stations	6
Maximum Operating Pressure	1000 psi
Inlet Port	(2) 1/2in female NPT
Outlet Port	(6) 3/8in female NPT
Mounting Hole Spacing	Wide

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MRA-6ED-W.pdf>  
See store item page for other formats.