

MRA-9ED Cut Sheet

NITRA pneumatic valve manifold, aluminum, rectangular, 1000 psi maximum operating pressure, (9) stations, (2) 1/2in female NPT inlet(s), (9) 3/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRA-9ED>

Technical Specifications

Brand	NITRA
Item	Pneumatic Valve manifold
Material	Aluminum
Shape	Rectangular
Number of Stations	9
Maximum Operating Pressure	1000 psi
Inlet Port	(2) 1/2in female NPT
Outlet Port	(9) 3/8in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document