

# MRN-3CB Cut Sheet



NITRA pneumatic or water valve manifold, Nylon 6, white, rectangular, 200 psi maximum operating pressure, (3) stations, (2) 1/4in female NPT inlet(s), (3) 1/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRN-3CB>

## Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas or water
Material	Nylon 6
Color	White
Shape	Rectangular
Number of Stations	3
Maximum Operating Pressure	200 psi
Inlet Port	(2) 1/4in female NPT
Outlet Port	(3) 1/8in female NPT
Mounting Hole Spacing	Standard

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MRN-3CB.pdf>  
See store item page for other formats.