

MRN-6CB Cut Sheet



NITRA pneumatic or water valve manifold, Nylon 6, rectangular, 200 psi maximum operating pressure, (6) stations, (2) 1/4in female NPT inlet(s), (6) 1/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRN-6CB>

Technical Specifications

Brand	NITRA
Item	Pneumatic or water Valve manifold
Material	Nylon 6
Shape	Rectangular
Number of Stations	6
Maximum Operating Pressure	200 psi
Inlet Port	(2) 1/4in female NPT
Outlet Port	(6) 1/8in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document