

MRP-10CB Cut Sheet



NITRA pneumatic or water valve manifold, polypropylene (PP), white, rectangular, 150 psi maximum operating pressure, (10) stations, (2) 1/4in female NPT inlet(s), (10) 1/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRP-10CB>

Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas or water
Material	Polypropylene (PP)
Color	White
Shape	Rectangular
Number of Stations	10
Maximum Operating Pressure	150 psi
Inlet Port	(2) 1/4in female NPT
Outlet Port	(10) 1/8in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MRP-10CB.pdf>
See store item page for other formats.