

MRP-7DC Cut Sheet



NITRA pneumatic or water valve manifold, polypropylene (PP), rectangular, 150 psi maximum operating pressure, (7) stations, (2) 3/8in female NPT inlet(s), (7) 1/4in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRP-7DC>

Technical Specifications

Brand	NITRA
Item	Pneumatic or water Valve manifold
Material	Polypropylene (PP)
Shape	Rectangular
Number of Stations	7
Maximum Operating Pressure	150 psi
Inlet Port	(2) 3/8in female NPT
Outlet Port	(7) 1/4in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document