

MRS-10DC Cut Sheet

NITRA pneumatic valve manifold, stainless steel, silver, rectangular, 3500 psi maximum operating pressure, (10) stations, (2) 3/8in female NPT inlet(s), (10) 1/4in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRS-10DC>



Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas
Material	Stainless steel
Color	Silver
Shape	Rectangular
Number of Stations	10
Maximum Operating Pressure	3500 psi
Inlet Port	(2) 3/8in female NPT
Outlet Port	(10) 1/4in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MRS-10DC.pdf>
See store item page for other formats.