

MRT12M-12R Cut Sheet



NITRA pneumatic push-to-connect fitting, male, run tee, rotating, thermoplastic (PBT) body, nickel-plated brass threads, (2) 12mm tube to R1/2 BSPT connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRT12M-12R>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Gender	Male
Fitting Type	Run tee
Fitting Function	Rotating
Body Material	Thermoplastic (PBT)
Thread Material	Nickel-plated brass
Thread Sealant	Yes
Connection	(2) 12mm push-to-connect and R1/2 BSPT
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document