

MS0-00-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic, diffuse with background suppression, 50mm sensing distance, selectable light-on/dark-on, NPN/PNP, 80 Hz switching frequency, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS0-00-0E>

Technical Specifications

Brand	AutomationDirect	Number of Wires	4
Item	Photoelectric sensor	Switching Output	NPN/PNP
Shape	Tubular	Sensing Distance	50mm
Barrel Type	Threaded	Operation Mode	Selectable light-on/dark-on
Housing Size	18mm diameter x 80mm body	Switching Frequency	80 Hz
IP Rating	IP67	Light Emission	Infrared
Housing Material	Plastic	Connection	4-pin M12 quick-disconnect
Sensing Method	Diffuse with background suppression	Includes	Mounting hardware
Operating Voltage	10-30 VDC	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document