

MS10M-14R-B Cut Sheet



NITRA pneumatic push-to-connect fitting, male, straight, nickel-plated brass body, nickel-plated brass threads, thread sealant, 10mm push-to-connect to R1/4 BSPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS10M-14R-B>

Technical Specifications

| | |
|--------------------------------|------------------------------------|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Gender | Male |
| Fitting Type | Straight |
| Body Material | Nickel-plated brass |
| Thread Material | Nickel-plated brass |
| Thread Sealant | Yes |
| Connection | 10mm push-to-connect and R1/4 BSPT |
| Operating Pressure | 0 to 300 psi |
| Operating Temperature | 0 to 175 deg F |
| Quantity per Pack | 5 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MS10M-14R-B.pdf>
See store item page for other formats.