

# MS12-38N-B Cut Sheet



NITRA pneumatic push-to-connect fitting, male, straight, nickel-plated brass body, nickel-plated brass threads, thread sealant, 1/2in push-to-connect to 3/8in NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS12-38N-B>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Fitting
<b>Working Fluid</b>	Air or inert gas
<b>Fitting Connection Type</b>	Push-to-connect
<b>Gender</b>	Male
<b>Fitting Type</b>	Straight
<b>Body Material</b>	Nickel-plated brass
<b>Thread Material</b>	Nickel-plated brass
<b>Thread Sealant</b>	Yes
<b>Connection</b>	1/2in push-to-connect and 3/8in NPT
<b>Operating Pressure</b>	0 to 300 psi
<b>Operating Temperature</b>	0 to 175 deg F
<b>Quantity per Pack</b>	5
<b>For Use With</b>	Flexible pneumatic tubing

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/MS12-38N-B.pdf>  
See store item page for other formats.