

# MS12-38N-P Cut Sheet



HydroMode potable water push-to-connect fitting, male, straight, acetal body, acetal threads, (1) 1/2in tube to (1) 3/8in male NPT connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS12-38N-P>

## Technical Specifications

Brand	HydroMode
Item	Potable water Push-to-connect Fitting
Gender	Male
Fitting Type	Straight
Body Material	Acetal
Thread Material	Acetal
Port Connection Info	(1) 1/2in tube to (1) 3/8in male NPT
Operating Pressure	145 psi
Operating Temperature	32 to 158 deg F
Agency Approval	NSF/ANSI 61
Quantity per Pack	5

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>