

MS25-40 Cut Sheet



AutomationDirect MS25 series manual motor protector, pushbutton, 0.4A, thermal overload, 0.25-0.4A adjustable, 5A instantaneous trip rating, open, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS25-40>

Technical Specifications

Brand	AutomationDirect	Number of Poles	3
Series	MS25	Power Poles	(3) N.O.
Item	Motor protector	Trip Class	Trip Class 10
Starter Type	Manual	Phase Loss Sensitive	Yes
Actuator Type	Pushbutton	Ground Fault Protection	No
Amperage Rating	0.4A	SCCR Rating	5kA SCCR
Voltage Rating	600 VAC	UL Rating	UL 508 rated
Relay Type	Thermal overload	Enclosure Type	Open
Operation Type	Bi-metallic	Frame	45mm
Full Load Amperage Range	0.25-0.4A adjustable	Mounting	35mm DIN rail or panel
Instantaneous Trip Rating	5A	Connection	Screw terminal

Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document