

MS6M-14R-SS Cut Sheet



NITRA pneumatic push-to-connect fitting, straight, 316 stainless steel body, 316 stainless steel threads, (1) R1/4 male BSPT to (1) 6mm push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS6M-14R-SS>

Technical Specifications

| | |
|--------------------------|--|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Fitting Type | Straight |
| Body Material | 316 stainless steel |
| Thread Material | 316 stainless steel |
| Thread Sealant | No |
| Fitting Measurement Type | Metric and SAE |
| Connection | (1) R1/4 male BSPT and (1) 6mm push-to-connect |
| Operating Pressure | -29.5in Hg to 290 psi |
| Operating Temperature | 32 to 390 deg F |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MS6M-14R-SS.pdf>
See store item page for other formats.