


MTPM-001-1M18 Cut Sheet



IronHorse MTPM DC permanent magnet motor, SCR-PWM rated, 1hp, 180 VDC, 1800rpm, TEFC, 56C frame, rolled steel, C-face/removable rigid base mount. Replacement brushes included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTPM-001-1M18>

Technical Specifications

Brand	IronHorse
Item	Motor
Series	MTPM
Voltage Type	DC
Motor Type	Permanent magnet
Motor Application	SCR-PWM rated
Horsepower Rating	1hp
Voltage Rating	180 VDC
Synchronous Speed	1800rpm
Nameplate RPM	1800rpm
Overload Type	None
Enclosure Type	TEFC
Shaft Type	Round with square key
Shaft Diameter	5/8in
Shaft Material	40 cold rolled heat treated hardness HB2800-320 steel

Motor Frame	56C
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP54
Constant Torque Rating	20:1
Service Factor	1.0
Integrated Brake	No
Junction Box Orientation	F3
Mounting	C-face/removable rigid base
Mounting Orientation	Horizontal or vertical
Includes	Replacement brushes
Manufacturer Part Number	WPMDC1-18-180V-56CB

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	247070
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document