

MTRJ-1P5-1AB36J Cut Sheet



IronHorse MTR standard efficiency AC induction motor, centrifugal jet pump, 1-1/2hp, 1-phase, 115/230 VAC, 3600rpm, TEFC, 56J frame, rolled steel, C-face/removable rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTRJ-1P5-1AB36J>

Technical Specifications

Brand	IronHorse
Item	Motor
Series	MTR
Efficiency Group	Standard efficiency
Efficiency	78.5
Voltage Type	AC
Motor Type	Induction
Motor Application	Centrifugal jet pump
Horsepower Rating	1-1/2hp
Number of Phases	1
Voltage Rating	115/230 VAC
Synchronous Speed	3600rpm
Nameplate RPM	3450rpm
Overload Type	Automatic
Enclosure Type	TEFC

Shaft Type	Round threaded 20 UNF-2A
Shaft Diameter	5/8in
Shaft Material	AISI 420 stainless steel
Motor Frame	56J
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP43
Service Factor	1.15
Integrated Brake	No
NEMA Design	Design L
Junction Box Orientation	F1
Mounting	C-face/removable rigid base
Mounting Orientation	Horizontal or vertical

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	256950
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document