

MTW12OR Cut Sheet



Atlas Wire MTW hook-up wire, single conductor, 12 AWG, 65-stranded, bare copper, PVC conductor insulation material, orange, 600V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTW12OR>

Technical Specifications

Brand	Atlas Wire
Item	Wire
Wire/Cable Type	MTW
UL Wire/Cable Type	MTW and AWM
Applicable Standards	UL 758, UL 1015, UL 1032, UL 1230, UL 1011, UL 1013, UL 1335, UL 1426 and CSA C22.2 No. 210
Application	Hook-up
Flexibility	Flexible
Voltage Rating	600V
Conductors	Single conductor

Conductor Size	12 AWG
Conductor Stranding	65-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Orange
Nominal Overall Cable Diameter	0.157in
Bulk Length	500ft spool

Agency Approvals

UL Listed File #	E215651
UL Recognized File #	E25635
UL Hazardous File #	None
CE	None
CSA File #	038335
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement