

MTW18BK25 Cut Sheet



Atlas Wire MTW hook-up wire, single conductor, 18 AWG, 16-stranded, bare copper, PVC conductor insulation material, black, 600V, 2500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTW18BK25>

Technical Specifications

Brand	Atlas Wire
Item	Wire
Wire/Cable Type	MTW
UL Wire/Cable Type	MTW and AWM
Applicable Standards	UL 758, UL 1063, UL 1015, UL 1230, UL 1011, UL 1013, UL 1335, UL 1032 and CSA C22.2 No. 210
Application	Hook-up
Flexibility	Flexible
Voltage Rating	600V
Conductors	Single conductor

Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black
Nominal Overall Cable Diameter	0.11in
Bulk Length	2500ft reel

Agency Approvals

UL Listed File #	E80256
UL Recognized File #	E25635
UL Hazardous File #	None
CE	None
CSA File #	038335
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement