

MTW22BK10 Cut Sheet



Atlas Wire MTW hook-up wire, single conductor, 22 AWG, 7-stranded, bare copper, PVC conductor insulation material, black, 600V, 1000ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTW22BK10>

Technical Specifications

Brand	Atlas Wire
Item	Wire
Wire/Cable Type	MTW
UL Wire/Cable Type	AWM and MTW
Applicable Standards	UL 758, UL 1015, UL 1230, UL 1032, CSA C22.2 No. 210, UL 1011, UL 1013 and UL 1335
Application	Hook-up
Flexibility	Flexible
Voltage Rating	600V
Conductors	Single conductor

Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black
Nominal Overall Cable Diameter	0.092in
Bulk Length	1000ft spool

Agency Approvals

UL Listed File #	E80256
UL Recognized File #	E25635
UL Hazardous File #	none
CE	None
CSA File #	038335
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement