

MTW4-0BK-1 Cut Sheet



Direct Wire flexible power cable, unshielded, MTW and THHW, single conductor, 4/0 AWG, bare copper, PVC conductor insulation material, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTW4-0BK-1>

Technical Specifications

Brand	Direct Wire
Item	Cable
Wire/Cable Type	Power
UL Wire/Cable Type	MTW and THHW
Applicable Standards	UL 1063, UL 83 and UL 1426
Application	Power
Flexibility	Flexible
Voltage Rating	600V (MTW, THHW), 1000V (AWM Style 10269)
Conductors	Single conductor
Conductor Size	4/0 AWG
Conductor Stranding	2109-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black
Shielding	Unshielded
Nominal Overall Cable Diameter	0.695in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 80ft = 14 x 7in Reel, 81 to 115ft = 14 x 10in Reel, 116 to 175ft = 16 x 10in Reel, 176 to 245ft = 18 x 10in Reel, 246 to 320ft = 18 x 13in Reel, 321 to 720ft = 24 x 17in Wooden Reel, 721 to 1150ft = 30 x 17in Wooden Reel, 1151 to 2500ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E507148, E507499
UL Recognized File #	E361079
UL Hazardous File #	None
CE	None
CSA File #	300528
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement