

MV4-A0-0A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared, 200mm sensing distance, light-on, 25 Hz switching frequency, plastic housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MV4-A0-0A>

Technical Specifications

Brand	AutomationDirect	Number of Wires	3
Item	Photoelectric sensor	Sensing Distance	200mm
Shape	Tubular	Operation Mode	Light-on
Barrel Type	Threaded	Switching Frequency	25 Hz
Housing Size	18mm diameter x 80mm body	Light Emission (NP)	Infrared
IP Rating	IP67	Cable Length	6.5ft/2m
Housing Material	Plastic	Connection	Pigtail
Sensing Method	Diffuse	Conductor Size	22 AWG
Operating Voltage	20-253 VAC		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E130644
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document