

MV4-A0-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared, 200mm sensing distance, light-on, 25 Hz switching frequency, plastic housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MV4-A0-0E>

Technical Specifications

Brand	AutomationDirect	Operating Voltage	20-253 VAC
Item	Photoelectric sensor	Number of Wires	3
Shape	Tubular	Sensing Distance	200mm
Barrel Type	Threaded	Operation Mode	Light-on
Housing Size	18mm diameter x 80mm body	Switching Frequency	25 Hz
IP Rating	IP67	Light Emission (NP)	Infrared
Housing Material	Plastic	Connection	4-pin M12 quick-disconnect
Sensing Method	Diffuse	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E130644
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document