

MV6-A0-0A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared light emission, 400mm sensing distance, light-on, 25 Hz switching frequency, plastic housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MV6-A0-0A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 80mm body
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Operating Voltage	20-253 VAC
Number of Wires	3
Sensing Distance	400mm
Operation Mode	Light-on
Switching Frequency	25 Hz
Light emission	Infrared
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	22 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	E130644
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document