

# MY38-12N Cut Sheet



NITRA pneumatic push-to-connect fitting, Y, rotating, thermoplastic (PBT) body, nickel-plated brass threads, thread sealant, (1) 1/2in male NPT to (2) 3/8in push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MY38-12N>

## Technical Specifications

|                                |                     |
|--------------------------------|---------------------|
| <b>Brand</b>                   | NITRA               |
| <b>Item</b>                    | Fitting             |
| <b>Working Fluid</b>           | Air or inert gas    |
| <b>Fitting Connection Type</b> | Push-to-connect     |
| <b>Fitting Type</b>            | Y                   |
| <b>Fitting Function</b>        | Rotating            |
| <b>Body Material</b>           | Thermoplastic (PBT) |
| <b>Thread Material</b>         | Nickel-plated brass |

|                                 |  |
|---------------------------------|--|
| <b>Thread Sealant</b>           | Yes  |
| <b>Fitting Measurement Type</b> | SAE  |
| <b>Connection</b>               | (1) 1/2in male NPT and (2) 3/8in push-to-connect |
| <b>Operating Pressure</b>       | -29.5in Hg to 150 psi                            |
| <b>Operating Temperature</b>    | 32 to 140 deg F                                  |
| <b>Quantity per Pack</b>        | 5  |
| <b>For Use With</b>             | Flexible pneumatic tubing                        |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MY38-12N.pdf>  
See store item page for other formats.