

N12483008 Cut Sheet



Wiegmann enclosure, NEMA 12/13, 48 x 30 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, (3) plated steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N12483008>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
NEMA Rating	12/13	Finish	Powder coat
Nominal Enclosure Dimensions	48 x 30 x 8in (HxWxD)	Cover Type	Single-door
Enclosure Height	48.00in	Hinge Type	Continuous hinge
Enclosure Width	30.00in	Number of Hinges Per Door	1
Enclosure Depth	9.03in	Latch Type	(3) plated steel clamps
Mounting	Wall	Padlock Attachment Type	Padlock hasp and staple
Integral Mounting Feet	Yes	Padlockable	Yes
Integral Mounting Flange	No	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document