

# N12BLK100 Cut Sheet



NITRA pneumatic tubing, nylon 12, black, 1/2in outside diameter, 0.375in inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N12BLK100>

---

## Technical Specifications

|                              |                   |
|------------------------------|-------------------|
| <b>Brand</b>                 | NITRA             |
| <b>Item</b>                  | Pneumatic Tubing  |
| <b>Material</b>              | Nylon 12          |
| <b>Color</b>                 | Black             |
| <b>Outside Diameter</b>      | 1/2in             |
| <b>Inside Diameter</b>       | 0.375in           |
| <b>UV stabilized</b>         | No                |
| <b>Working Length</b>        | 100ft package     |
| <b>Operating Pressure</b>    | 240 psi           |
| <b>Operating Temperature</b> | -60 to +200 deg F |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |