

# N12MBLU100 Cut Sheet



NITRA pneumatic tubing, nylon 12, blue, 12mm outside diameter, 10mm inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N12MBLU100>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Tubing
<b>Material</b>	Nylon 12
<b>Color</b>	Blue
<b>Outside Diameter</b>	12mm
<b>Inside Diameter</b>	10mm
<b>UV stabilized</b>	No
<b>Working Length</b>	100ft package
<b>Operating Pressure</b>	200 psi
<b>Operating Temperature</b>	-60 to +200 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>