

N12MBLU100 Cut Sheet



NITRA pneumatic tubing, nylon 12, blue, 12mm outside diameter, 10mm inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N12MBLU100>

Technical Specifications

Brand	NITRA
Item	Tubing
Working Fluid	Air or inert gas
Material	Nylon 12
Color	Blue
Outside Diameter	12mm
Inside Diameter	10mm
UV stabilized	No
Working Length	100ft package
Operating Pressure	200 psi
Operating Temperature	-60 to +200 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document