

N14NAT500 Cut Sheet



NITRA pneumatic tubing, nylon 12, natural, 1/4in outside diameter, 0.180in inside diameter, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N14NAT500>

Technical Specifications

Brand	NITRA
Item	Pneumatic Tubing
Material	Nylon 12
Color	Natural
Outside Diameter	1/4in
Inside Diameter	0.180in
UV stabilized	No
Working Length	500ft reel
Operating Pressure	290 psi
Operating Temperature	-60 to +200 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document