

N1C121208 Cut Sheet



Wiegmann enclosure, NEMA 1, 12 x 12 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N1C121208>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1
Nominal Enclosure Dimensions	12 x 12 x 8in (HxWxD)
Enclosure Height	12.50in
Enclosure Width	12.50in
Enclosure Depth	8.14in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	1/4-turn flush-mounted latch
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document