

N1WS20166 Cut Sheet



Hammond enclosure, 3-piece assembly, NEMA 1, 20 x 16 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N1WS20166>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
3-Piece Assembly	Yes
NEMA Rating	1
IP Rating	IP20
Nominal Enclosure Dimensions	20 x 16 x 6in (HxWxD)
Enclosure Height	20.28in
Enclosure Width	16.28in
Enclosure Depth	6.16in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes

Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Slip hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn flush-mounted latch
Number Of Latches	1
Padlockable	No
Keylocking	No
Additional Information	Three-piece construction

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document