

N302410RT Cut Sheet



Stahlin N series enclosure, NEMA 1/3R, 30 x 24 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N302410RT>

Technical Specifications

Brand	Stahlin	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	N	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	No	Material	Fiberglass reinforced polyester
3-Piece Assembly	No	Color	Gray
Vented	No	Cover Type	Single-door
NEMA Rating	1/3R	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	30 x 24 x 10in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	33.41in	Latch Type	(2) twist-lock latches
Enclosure Width	26.32in	Padlock Attachment Type	Padlock hasp and staple
Enclosure Depth	11.95in	Shelf	No
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/N302410RT.pdf>
See store item page for other formats.