N363010HWT Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Stahlin N series enclosure, NEMA 1/3/3R/4X/12, 36 x 30 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, twist-lock latch, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/N363010HWT

Technical Specifications

Brand	Stahlin
Series	N
Item	Enclosure
Subpanel	Purchase subpanel separately
NEMA Rating	1/3/3R/4X/12
IP Rating	IP66
Nominal Enclosure Height	36in
Nominal Enclosure Width	30in
Nominal Enclosure Depth	10in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No

Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	Twist-lock latch
Number Of Latches	5
Padlockable	Yes
Padlock Attachment Type	Padlock hasp and staple
Keylocking	No
Shelf	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/N363010HWT.pdf
See store item page for other formats.