

N412202208CD Cut Sheet



Wiegmann Ultimate series disconnect enclosure, NEMA 4/12/13, right flange, 20 x 22 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412202208CD>

Technical Specifications

Brand	Wiegmann	Knockouts	No
Item	Disconnect enclosure	Material	Carbon steel
Series	Ultimate	Color	ANSI 61 gray
Slope Top	No	Finish	Powder coat
NEMA Rating	4/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Concealed hinges
Disconnect Mounting	Right flange	Number of Hinges Per Door	2
Nominal Enclosure Dimensions	20 x 22 x 8in (HxWxD)	Latch Type	2-point padlocking handle
Enclosure Height	20.00in	Padlockable	Yes
Enclosure Width	22.00in	Keylocking	No
Enclosure Depth	8.89in	Subpanel	Purchase subpanel separately
Mounting	Wall	For Use With	Most major brand disconnect switches and circuit breakers
Integral Mounting Feet	No	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Integral Mounting Flange	No		
Dual Access	No		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None