

N4122024081PTC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/12/13, 20 x 24 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N4122024081PTC>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Ultimate
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	20 x 24 x 8in (HxWxD)
Enclosure Height	20.00in
Enclosure Width	24.00in
Enclosure Depth	8.92in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1-point keylocking/padlocking combo handle
Shelf	No
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N4122024081PTC.pdf>
See store item page for other formats.