

N412202408C Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/12/13, 20 x 24 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412202408C>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Series | Ultimate |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 4/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 20 x 24 x 8in (HxWxD) |
| Enclosure Height | 20.00in |
| Enclosure Width | 24.00in |
| Enclosure Depth | 8.92in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|-------------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 2 |
| Latch Type | 1/4-turn semi-flush oil-tight latch |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |