

N412241606CLG Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/12/13, 24 x 16 x 6in (HxWxD), wall mount, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412241606CLG>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Ultimate	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	No	Color	RAL 7035 light gray
NEMA Rating	4/12/13	Finish	Powder coat
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	24 x 16 x 6in (HxWxD)	Hinge Type	Concealed hinges
Enclosure Height	24.00in	Number of Hinges Per Door	2
Enclosure Width	16.00in	Latch Type	1/4-turn semi-flush oil-tight latch
Enclosure Depth	6.92in	Padlockable	No
Mounting	Wall	Keylocking	No
Integral Mounting Feet	No		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document