

N412302412SSC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/4X/12/13, 30 x 24 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412302412SSC>

Technical Specifications

Brand	Wiegmann	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Ultimate	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	No. 3 intermediate polished
NEMA Rating	4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	30 x 24 x 12in (HxWxD)	Number of Hinges Per Door	2
Enclosure Height	30.00in	Latch Type	1/4-turn semi-flush oil-tight latch
Enclosure Width	24.00in	Shelf	No
Enclosure Depth	12.92in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N412302412SSC.pdf>
See store item page for other formats.