

N412362412SS3PTC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4X/12/13, 36 x 24 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412362412SS3PTC>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Ultimate
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	36 x 24 x 12in (HxWxD)
Enclosure Height	36.00in
Enclosure Width	24.00in
Enclosure Depth	12.92in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	3-point 316L padlocking handle
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N412362412SS3PTC.pdf>
See store item page for other formats.