

N412423212CD Cut Sheet



Wiegmann Ultimate series disconnect enclosure, NEMA 4/12/13, right flange, 42 x 32 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412423212CD>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Series	Ultimate
Slope Top	No
NEMA Rating	4/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	42 x 32 x 12in (HxWxD)
Enclosure Height	42.00in
Enclosure Width	32.00in
Enclosure Depth	12.89in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately
For Use With	Most major brand disconnect switches and circuit breakers
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document