

# N412423610SSC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/4X/12/13, 42 x 36 x 10in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 1/4-turn semi-flush oil-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412423610SSC>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Wiegmann                     |
| <b>Item</b>                         | Enclosure                    |
| <b>Series</b>                       | Ultimate                     |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 4/4X/12/13                   |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 42 x 36 x 10in (HxWxD)       |
| <b>Enclosure Height</b>             | 42.00in                      |
| <b>Enclosure Width</b>              | 36.00in                      |
| <b>Enclosure Depth</b>              | 10.92in                      |
| <b>Mounting</b>                     | Wall                         |

|                                  |                                     |
|----------------------------------|-------------------------------------|
| <b>Integral Mounting Feet</b>    | No                                  |
| <b>Integral Mounting Flange</b>  | No                                  |
| <b>Dual Access</b>               | No                                  |
| <b>Knockouts</b>                 | No                                  |
| <b>Material</b>                  | 304 stainless steel                 |
| <b>Finish</b>                    | No. 3 intermediate polished         |
| <b>Cover Type</b>                | Single-door                         |
| <b>Hinge Type</b>                | Concealed hinges                    |
| <b>Number of Hinges Per Door</b> | 3                                   |
| <b>Latch Type</b>                | 1/4-turn semi-flush oil-tight latch |
| <b>Padlockable</b>               | No                                  |
| <b>Keylocking</b>                | No                                  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |