

N412603812CDSS Cut Sheet



Wiegmann Ultimate series disconnect enclosure, NEMA 4/4X/12/13, right flange, 60 x 38 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412603812CDSS>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Series	Ultimate
Slope Top	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Height	60in
Nominal Enclosure Width	38in
Nominal Enclosure Depth	12.88in
Mounting	Wall
Integral Mounting Feet	No

Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N412603812CDSS.pdf>
See store item page for other formats.