

N412D304210SSC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 3R/4/4X/12/13, 30 x 42 x 10in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412D304210SSC>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Ultimate
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	30 x 42 x 10in (HxWxD)
Enclosure Height	30.00in
Enclosure Width	42.00in
Enclosure Depth	10.92in
Mounting	Wall
Integral Mounting Feet	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	1
Latch Type	3-point keylocking/padlocking combo handle
Number Of Latches	2
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document