

N412D364812SSC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 3R/4/4X/12/13, 36 x 48 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412D364812SSC>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Series | Ultimate |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 36 x 48 x 12in (HxWxD) |
| Enclosure Height | 36.00in |
| Enclosure Width | 48.00in |
| Enclosure Depth | 12.92in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|--|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 1 |
| Latch Type | 3-point keylocking/padlocking combo handle |
| Number Of Latches | 2 |
| Shelf | No |
| Padlockable | Yes |
| Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N412D364812SSC.pdf>
See store item page for other formats.