

# N412D426012C Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 3R/4/12/13, 42 x 60 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412D426012C>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Series                   | Ultimate                     |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 3R/4/12/13                   |
| IP Rating                | IP66                         |
| Nominal Enclosure Height | 42in                         |
| Nominal Enclosure Width  | 60in                         |
| Nominal Enclosure Depth  | 12in                         |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | No                           |
| Dual Access              | No                           |

|                           |                                            |
|---------------------------|--------------------------------------------|
| Knockouts                 | No                                         |
| Bottom Gland Plate        | No                                         |
| Material                  | Carbon steel                               |
| Color                     | ANSI 61 gray                               |
| Finish                    | Powder coat                                |
| Cover Type                | 2-door                                     |
| Hinge Type                | Concealed hinges                           |
| Number of Hinges Per Door | 1                                          |
| Latch Type                | 3-point keylocking/padlocking combo handle |
| Number Of Latches         | 2                                          |
| Padlockable               | Yes                                        |
| Keylocking                | Yes                                        |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/N412D426012C.pdf>  
See store item page for other formats.