

N4302412 Cut Sheet



Wiegmann enclosure, NEMA 4/12/13, 30 x 24 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, (7) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N4302412>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	30 x 24 x 12in (HxWxD)
Enclosure Height	30.00in
Enclosure Width	24.00in
Enclosure Depth	13.03in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(7) stainless steel clamps
Padlock Attachment Type	Padlock hasp and staple
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N4302412.pdf>
See store item page for other formats.