

N4D747224 Cut Sheet



Wiegmann enclosure, NEMA 3/4/12, 74 x 72 x 24in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, (24) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N4D747224>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3/4/12
Nominal Enclosure Height	74in
Nominal Enclosure Width	72in
Nominal Enclosure Depth	24in
Mounting	Floor
Dual Access	No
Knockouts	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(24) stainless steel clamps
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N4D747224.pdf>
See store item page for other formats.