

N8MBLK100 Cut Sheet



NITRA pneumatic tubing, nylon 12, black, 5/16in (8mm) outside diameter, 6mm inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N8MBLK100>

Technical Specifications

Brand	NITRA
Item	Tubing
Working Fluid	Air or inert gas
Material	Nylon 12
Color	Black
Outside Diameter	5/16in (8mm)
Inside Diameter	6mm
UV stabilized	No
Working Length	100ft package
Operating Pressure	250 psi
Operating Temperature	-60 to +200 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document